

Garant**Disc brush, ceramic grit (CER), Ø 100 mm, Grit: 80****Order data**

Order number	575032 80
GTIN	4045197892744
Item class	51P

Description**Version:**

With longitudinal groove for clamping on face mill arbors (DIN 6357) and combination face mill adapters (DIN 6358).

Disc brushes with **extremely tightly packed abrasive bristles (right to the edge of the brush)** embedded in the plastic pad. The bristles support each other, giving a **highly stable shape**. Very long working life.

Nylon bristles with **ceramic grit content**. More aggressive abrasive effect.

Advantage:

- **Workpiece rework directly after the machining process.**
- **Reproducible results due to constantly exposed grinding grit.**
- **Good process reliability thanks to high shape stability and shape accuracy.**
- **Quick and secure installation without further accessories.**
- **Very low radial run-out.**

Application:

On **CNC machining centres** and when used by **robots**, preferably **wet grinding** with cooling lubricant. Machining of flat components: precise **deburring**, **edge rounding**, **finish machining** after milling, **surface finishing** e.g. of sealing and mating faces.

Note:

Special versions available on request.

Technical description

Grit	80
Bristle thickness	1.2 mm
Grit designation	coarse
Infeed	0.8 (fine) – 1.5 (coarse) mm
Feed	3000 - 5500 mm/min
Product name attribute	Ø 100 mm
Brush Ø D ₁	100 mm
Disc dia. D ₂	106 mm
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Working area Ø	100 mm
Bore Ø d ₁	22 with groove mm
Length of brush section H ₁	35 mm
recommended speed	1400 - 1700 min ⁻¹
maximum speed	3500 min ⁻¹
Type of product	Disc brush

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable only under restricted conditions		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
GG(G)	suitable		

wet maximum	suitable
dry	suitable only under restricted conditions

Accessories

Tightening screw with internal cooling for mandrel Ø 22 mm

575096 22