

## Garant

### Hole saw, bi-metal, Diameter: 27 mm



#### Order data

Order number	589010 27
GTIN	4045197158376
Item class	51S

#### Description

##### Version:

**Robust unbreakable construction** with variable toothing on flexible special steel body (bimetal). The reinforced stiff base is equipped with thread and drive pin holes (from Ø 32 mm) for secure mounting on the arbor. The high quality of the HSS teeth, the teeth geometry and the tight manufacturing tolerances guarantee the best cutting performance and tool life.

- **Vario toothing 4/6 tpi for low vibration.**
- **Maximum depth of cut for all sizes 38 mm.**
- **Precision ground teeth – very quick sawing and clean cut edges.**

##### Application:

On pillar drills, lathes or hand-held power drills at the appropriate speed. For cutting circular holes from thin-walled to thick-walled material with a flat or convex workpiece surface. Suitable for all materials such as steel, **stainless steel**, brass, copper, cast iron, light metal, wood, plasterboard and plastic panels etc. Use of lubricant will give increased tool life (metals).

##### Recommendation:

The use of cutting oil such as No. 084205 size 0.25 extends the service life and permits more rapid progress through the material.

##### Note:

**Arbors and hole saws are compatible with all commercially available bi-metal hole saws apart from Bosch SDS.**

**For hole saws for stone see No. 788000, 788040, 788050.**

**For carbide hole saws for steel see No. 118400, 118500, 119000.**

TPI: 4 / 6

recommended speed steel: 325 min<sup>-1</sup>

recommended speed INOX: 180 min<sup>-1</sup>

recommended speed aluminium: 480 min<sup>-1</sup>

---

## Technical description

recommended speed INOX	180 min <sup>-1</sup>
recommended speed steel	325 min <sup>-1</sup>
Diameter	27 mm
recommended speed aluminium	480 min <sup>-1</sup>
TPI	4 / 6
Type of product	Hole saw

---

## Accessories

Quick-change mounting shank Type 30	589314 30
Centre drill HSS Type 6KT	589430 6KT
Centre drill carbide-tipped Type 6KT	589432 6KT
Shank Type 30	589310 30