

**Garant**
**Hole saw set, Type: 16-76**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 589710 16-76  |
| GTIN         | 4045197158772 |
| Item class   | 51S           |

**Description**
**Version:**

Bi-metal hole saw set with popular hole saw diameters. HSS Vario tothing for smooth cutting and long service life.

With precision rigid foam inlay for secure retention and easy removal of the hole saws. Stackable modular bar.

**Supplied with:**

Impact-resistant plastic box with bi-metal hole saws, mounting shafts and centre drills.

Hole saw Ø: 16; 19; 22; 25; 29; 32; 35; 38; 44; 51; 68; 76 mm

Number of pieces: 19

Number of mounting shafts: 2

Number of centre drills: 5

**Technical description**

|                           |  |
|---------------------------|--|
| Hole saw Ø                | 16; 19; 22; 25; 29; 32; 35;<br>38; 44; 51; 68; 76 mm |
| Number of mounting shafts | 2  |
| Number of centre drills   | 5  |
| Number of pieces          | 19   |
| Type of product           | Hole saw   |

---

**Accessories**

|                                   |             |
|-----------------------------------|-------------|
| Modular box Type 4-2              | 630310 4-2  |
| Hole saw, bi-metal Diameter 51 mm | 589010 51   |
| Hole saw, bi-metal Diameter 29 mm | 589010 29   |
| Hole saw, bi-metal Diameter 76 mm | 589010 76   |
| Hole saw, bi-metal Diameter 68 mm | 589010 68   |
| Hole saw, bi-metal Diameter 25 mm | 589010 25   |
| Hole saw, bi-metal Diameter 35 mm | 589010 35   |
| Hole saw, bi-metal Diameter 22 mm | 589010 22   |
| Hole saw, bi-metal Diameter 38 mm | 589010 38   |
| Hole saw, bi-metal Diameter 32 mm | 589010 32   |
| Hole saw, bi-metal Diameter 19 mm | 589010 19   |
| Hole saw, bi-metal Diameter 16 mm | 589010 16   |
| Hole saw, bi-metal Diameter 44 mm | 589010 44   |
| Centre drill HSS Type 6KT         | 589428 6KT  |
| Shank Type 210S                   | 589305 210S |
| Shank Type 30                     | 589305 30   |