

**Double-ended open ring spanner, Width across flats: 17X19mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 619705 17X19  |
| GTIN         | 4045197673398 |
| Item class   | 62A           |

**Description****Version:**

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With oval, easy grip shaft, very strong. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

**Standard:**

**DIN 3118 / ISO 3318**

**Material:**

Chrome vanadium steel, chrome-plated.

**Technical description**

|                                     |                     |
|-------------------------------------|---------------------|
| Spanner length L                    | 213 mm              |
| maximum ring height $h_{1 \max}$    | 12 mm               |
| maximum ring $\varnothing D_1 \max$ | 31.2 mm             |
| Width across flats 2                | 19 mm               |
| maximum ring height $h_{2 \max}$    | 13 mm               |
| maximum ring $\varnothing D_2 \max$ | 33.3 mm             |
| Width across flats 1                | 17 mm               |
| Width across flats                  | metric              |
| Standard                            | DIN 3118 / ISO 3318 |
| Ring setting                        | 10 degrees          |

|                 |                       |
|-----------------|-----------------------|
| Material        | Chrome vanadium steel |
| Surface         | chrome-plated         |
| Type of product | Spanner               |