


Side cutter, bright finish, overall length: 140mm

Order data

Order number	725250 140
GTIN	4045197166319
Item class	72B

Description
Version:

Slim shape with induction hardened cutting edges (approx. 62 HRC).
Jaws bright finished, plastic coated handles.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity soft wire up to Ø	2.8 mm
overall length	140 mm
Cutting capacity hard wire up to Ø	1.8 mm
Standard	DIN ISO 5749
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chromium vanadium steel
Surface	bright finish
Heavy-duty diagonal side cutter	no
with selectable return spring	no

Type of product

Cutting pliers