

**Corner pipe wrench with S-form jaws, Pipe Ø: 1.1/2in****Order data**

Order number	810600 1.1/2
GTIN	4045197167057
Item class	82A

**Description****Version:**

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

**HOLEX** with **S-form jaws** for 3-point pipe support. (economy version).

**Material:**

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

**Technical description**

Jaw capacity	63 mm
overall length	420 mm
Pipe Ø	1.1/2 in
Jaw angle	45 degrees
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
S-jaw	yes
Swedish profile	yes
Type of product	Pipe wrench and water pump pliers

---

## Accessories

Knurled nut Type 1.1/2

810520 1.1/2