

**Corner pipe wrench with S-form jaws, Pipe Ø: 2in****Order data**

Order number	810600 2
GTIN	4045197167064
Item class	82A

Description**Version:**

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

HOLEX with **S-form jaws** for 3-point pipe support. (economy version).

Material:

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

Technical description

overall length	560 mm
Jaw capacity	80 mm
Pipe Ø	2 in
Jaw angle	45 degrees
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
S-jaw	yes
Swedish profile	yes
Type of product	Pipe wrench and water pump pliers

Accessories

Knurled nut Type 2

810520 2