



Corner pipe wrench with S-form jaws, Pipe Ø: 1.1/2in



Order data

Order number	810500 1.1/2
GTIN	4045197237477
Item class	82A

Description

Version:

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

HOLEX with **S-form jaws** for 3-point pipe support. Handles with **non-slip** plastic coating.

Material:

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

Technical description

Pipe Ø	1.1/2 in
Jaw capacity	63 mm
overall length	420 mm
Jaw angle	45 degrees
Type of handle	coated with non-slip plastic
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chrome vanadium steel
S-jaw	yes
Swedish profile	yes
Type of product	Pipe wrench and water pump pliers

Accessories

Knurled nut Type 1.1/2

810520 1.1/2