

Garant**Stepped jaw, mobile, for jaw width: 125mm****Order data**

Order number	361295 125
GTIN	4045197912428
Item class	310

Description**Version:**

Coated, hardened and ground. Fastening screws.

Application:

To take front jaws No. 361140-361151.

Material:

Hardened steel.

Suitable for:

No. 360400 125, 360465 125, 360500 125, 360510 125, 360565 125, 360605 125, 361302 125, 361290 125G together with Allmatic Titan 1 and Allmatic SC125.

Note:

The front jaws are attached using an M6 bolt.

Technical description

Jaw width b	125 mm
Height h ₁	19 mm
Jaw height h	39.5 mm
c ₁	59 mm
Jaw length l	82 mm

suitable for colour code	LC-GARANT
suitable for colour code	NC8
suitable for colour code	TC
suitable for colour code	Duo
suitable for colour code	Titan
suitable for colour code	Duo Plus
suitable for colour code	HiPo
suitable for colour code	HOLEX NC
suitable for colour code	LC
suitable for colour code	LCV125G
suitable for colour code	Titan2/TitanSense
c	24 mm
Type of product	Vice jaws