

Garant

Heavy-duty combination pliers, chrome-plated, with two-component grips, overall length: 180mm

**Order data**

Order number	700340 180
GTIN	4045197416919
Item class	71B

Description**Version:**

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); also suitable for piano wire.

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Standard:

DIN ISO 5746.

Material:

Special tool steel, drop-forged, and oil-hardened.

Technical description

Cutting capacity hard wire up to \varnothing	2.5 mm
overall length	180 mm
Cutting capacity piano wire up to \varnothing	2 mm
Standard	DIN ISO 5746
Handle	Multi-component covering with non-slip Haptoprene surface
Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel

Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers