

Garant
Steel boring bar A.. SCLDR, for indexable inserts CDCT, right-hand, Shank \varnothing / insert size: 4/S4mm

Order data

| | |
|--------------|---------------|
| Order number | 268717 4/S4 |
| GTIN | 4045197923714 |
| Item class | 21V |

Technical description

| | |
|--|-------------------------------|
| Pack of insert screws | 269028 10 |
| Clamping height L_2 | 3.58 mm |
| suitable indexable insert | CDCT S4010. |
| Overhang L_1 | 12 mm |
| Insert size | 4 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 4.57 mm |
| Centre offset L_3 | 2.41 mm |
| Overall length L | 65 mm |
| ISO code toolholder | A04X SCLDR/LS4 |
| Setting angle κ | 97 degrees |
| Shank $\varnothing D_s$ | 4 mm |
| Standard | Works standard |
| Application type | right-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring Bar |

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6