

**Garant**
**Steel boring bar A.. SCLDR, for indexable inserts CDCT, right-hand, Shank  $\varnothing$  / insert size: 5/S4mm**

**Order data**

Order number	268717 5/S4
GTIN	4045197923721
Item class	21V

**Technical description**

Overall length L	65 mm
Centre offset L <sub>3</sub>	2.95 mm
Overhang L <sub>1</sub>	15 mm
suitable indexable insert	CDCT S4010.
Insert size	4 mm
Clamping height L <sub>2</sub>	4.6 mm
Minimum pre-drill $\varnothing$ D <sub>min</sub>	5.78 mm
Pack of insert screws	269028 10
Setting angle $\kappa$	95 degrees
ISO code toolholder	A05X SCLDR/LS4
Shank $\varnothing$ D <sub>s</sub>	5 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

---

**Accessories**

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6