

Garant
Steel boring bar A.. SCLDR, for indexable inserts CDCT, right-hand, Shank \varnothing / insert size: 6/S4mm


Order data

Order number	268717 6/S4
GTIN	4045197923738
Item class	21V

Technical description

suitable indexable insert	CDCT S4010.
Setting angle κ	95 degrees
ISO code toolholder	A06X SCLDR/LS4
Clamping height L_2	5.54 mm
Overall length L	65 mm
Pack of insert screws	269028 10
Centre offset L_3	3.73 mm
Insert size	4 mm
Overhang L_1	18 mm
Minimum pre-drill $\varnothing D_{\min}$	6.92 mm
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6