

**Garant**

**Steel boring bar A.. SCLDL, for indexable inserts CDCT, left-hand, Shank  $\varnothing$  / insert size: 5/S4mm**


**Order data**

Order number	268718 5/S4
GTIN	4045197923769
Item class	21V

**Technical description**

Overhang $L_1$	15 mm
Insert size	4 mm
Centre offset $L_3$	2.95 mm
Clamping height $L_2$	4.6 mm
Pack of insert screws	269028 10
ISO code toolholder	A05X SCLDR/LS4
suitable indexable insert	CDCT S4010.
Minimum pre-drill $\varnothing D_{\min}$	5.78 mm
Overall length L	65 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	5 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

---

**Accessories**

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6