

Garant

Steel boring bar A.. SCLDL, for indexable inserts CDCT, left-hand, Shank \varnothing / insert size: 6/S4mm


Order data

Order number	268718 6/S4
GTIN	4045197923776
Item class	21V

Technical description

Setting angle κ	95 degrees
Insert size	4 mm
Clamping height L_2	5.54 mm
ISO code toolholder	A06X SCLDR/LS4
Pack of insert screws	269028 10
Centre offset L_3	3.73 mm
suitable indexable insert	CDCT S4010.
Overall length L	65 mm
Minimum pre-drill $\varnothing D_{\min}$	6.92 mm
Overhang L_1	18 mm
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6