

**Garant****Precision circlip pliers, Type: A1****Order data**

Order number	719870 A1
GTIN	4045197504104
Item class	71B

**Description****Version:**

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, blacked. Ground head. Plastic coated handles. Joint with **integral opening spring**. **Form A – straight jaws**.

**Advantage:**

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

**Application:**

For fitting and removing circlips.

**Standard:**

**DIN 5254 A und B** – für Außensicherungsringe.

Use of circlip pliers: Outer ring, straight

overall length: 140 mm

for external circlips  $\varnothing$ : 10 - 25 mm

Tip  $\varnothing$ : 1.3 mm

**Technical description**

Tip $\varnothing$	1.3 mm
for external circlips $\varnothing$	10 - 25 mm
overall length	140 mm

Shape	A
Standard	DIN 5254 A
Use of circlip pliers	Outer ring, straight
Jaw shape	straight
Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	black
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers