

**Garant**
**Precision circlip pliers, Type: J41**

**Order data**

Order number	719770 J41
GTIN	4045197504081
Item class	71B

**Description**
**Version:**

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, blacked. Ground head. Plastic coated handles.

**With inserted precision tips. Form D – 90° angled jaws.**

**Advantage:**

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

**Application:**

For fitting and removing Circlips.

**Standard:**

**DIN 5256 C und D** – für Innensicherungsringe.

**Technical description**

Tip Ø	3.2 mm
overall length	305 mm
Shape	D
for internal circlips Ø	85 - 140 mm
Standard	DIN 5256 D
Use of circlip pliers	Inner ring, angled
Jaw shape	90° angled

Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	black
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers