

Garant**Precision circlip pliers, Type: A31****Order data**

| | |
|--------------|---------------|
| Order number | 719870 A31 |
| GTIN | 4045197504173 |
| Item class | 71B |

Description**Version:**

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, blacked. Ground head. Plastic coated handles. Joint with **integral opening spring**. **Form B –90° angled jaws**.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing circlips.

Standard:

DIN 5254 A und B – für Außensicherungsringe.

Technical description

| | |
|-------------------------|-------------|
| Tip Ø | 2.3 mm |
| overall length | 210 mm |
| Shape | B |
| for external circlips Ø | 40 - 100 mm |
| Standard | DIN 5254 B |

| | |
|------------------------------------|--------------------|
| Use of circlip pliers | Outer ring, angled |
| Jaw shape | 90° angled |
| Handle | plastic coated |
| Material | Special steel |
| Material of point | Special steel |
| Surface | black |
| with over-expansion guard | no |
| Joint with integral opening spring | yes |
| Handle with self-grip mechanism | no |
| Exchangeable points | no |
| Type of product | Circlip Pliers |