

Garant

Steel boring bar A.. PCLNR 95°, for indexable inserts CN., right-hand, Shank Ø / insert size: 16/09mm


Order data

Order number	250036 16/09
GTIN	4045197925916
Item class	21T

Description
Version:

PCLNR 95° boring bars for indexable inserts CN..

Technical description

suitable indexable insert	CN.. 09T3..
Overall length L	150 mm
Clamping height L ₂	15.25 mm
Lever	259015 11
Centre offset L ₃	11 mm
Lever screw	259018 9
Insert size	9 mm
Setting angle κ	95 degrees
Minimum pre-drill Ø D _{min}	20 mm
ISO code toolholder	A16M PCLNR/L09
Shank Ø D _s	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2