

**Garant**

**Steel boring bar A.. PCLNL 95°, for indexable inserts CN., left-hand, Shank Ø / insert size: 16/09mm**


**Order data**

Order number	250037 16/09
GTIN	4045197925923
Item class	21T

**Description**
**Version:**

PCLNL 95° boring bars for indexable inserts CN..

**Technical description**

suitable indexable insert	CN.. 09T3..
Lever	259015 11
ISO code toolholder	A16M PCLNR/L09
Overall length L	150 mm
Setting angle $\kappa$	95 degrees
Clamping height $L_2$	15.25 mm
Centre offset $L_3$	11 mm
Lever screw	259018 9
Insert size	9 mm
Minimum pre-drill $\varnothing D_{min}$	20 mm
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2