

**Garant**

**Clamping toolholder SVJBL 93°, for indexable inserts VB., left-hand, Shank / insert size: 12/11mm**



### Order data

Order number	261109 12/11
GTIN	4045197929112
Item class	21T

### Technical description

Functional width L <sub>4</sub>	16 mm
Shank size	12 mm
Overall length L	80 mm
suitable indexable insert	VB.. 1103..
Insert size	11 mm
Pack of insert screws	269028 22
ISO code toolholder	SVJBR/L 1212F11
Head length L <sub>1</sub>	21.5 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8