

Garant

Clamping toolholder SVJBR 93°, for indexable inserts VB., right-hand, Shank / insert size: 12/11mm



Order data

Order number	261108 12/11
GTIN	4045197929105
Item class	21T

Technical description

Shank size	12 mm
suitable indexable insert	VB.. 1103..
Pack of insert screws	269028 22
Functional width L_4	16 mm
Head length L_1	21.5 mm
Insert size	11 mm
ISO code toolholder	SVJBR/L 1212F11
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8