

Garant
Clamping toolholder SCSCR 45°, for indexable inserts CC., right-hand, Shank / insert size: 8/06mm

Order data

Order number	260000 8/06
GTIN	4045197929129
Item class	21T

Technical description

Functional width L ₄	10 mm
Shank size	8 mm
Overall length L	60 mm
Head length L ₁	12 mm
Pack of insert screws	269028 22
Insert size	6 mm
ISO code toolholder	SCSCR/L 0808D06
suitable indexable insert	CC.. 0602..
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8