

Garant
Clamping toolholder SCSCR 45°, for indexable inserts CC., right-hand, Shank / insert size: 16/12mm

Order data

Order number	260000 16/12
GTIN	4045197929174
Item class	21T

Technical description

Functional width L ₄	20 mm
ISO code toolholder	SCSCR/L 1616H12
Shim screw	269013 5
Insert size	12 mm
Pack of insert screws	269028 20
Overall length L	101 mm
Head length L ₁	22 mm
Shim	269005 6
Shank size	16 mm
suitable indexable insert	CC.. 1204..
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 20	269028 20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15