

Garant
Clamping toolholder SCSCCL 45°, for indexable inserts CC.., left-hand, Shank / insert size: 8/06mm

Order data

Order number	260001 8/06
GTIN	4045197929204
Item class	21T

Technical description

Pack of insert screws	269028 22
Functional width L ₄	10 mm
Overall length L	60 mm
ISO code toolholder	SCSCR/L 0808D06
Head length L ₁	12 mm
suitable indexable insert	CC.. 0602..
Shank size	8 mm
Insert size	6 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8