

Garant
Clamping toolholder SCSCCL 45°, for indexable inserts CC., left-hand, Shank / insert size: 20/12mm

Order data

Order number	260001 20/12
GTIN	4045197929297
Item class	21T

Technical description

Head length L ₁	24 mm
Shim	269005 6
Overall length L	126 mm
Shank size	20 mm
Pack of insert screws	269028 20
ISO code toolholder	SCSCR/L 2020K12
Functional width L ₄	25 mm
Shim screw	269013 5
suitable indexable insert	CC.. 1204..
Insert size	12 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15