

Garant

Clamping toolholder SCSCCL 45°, for indexable inserts CC., left-hand, Shank / insert size: 16/12mm



Order data

Order number	260001 16/12
GTIN	4045197929273
Item class	21T

Technical description

Shim screw	269013 5
Overall length L	101 mm
Functional width L ₄	20 mm
Shim	269005 6
Pack of insert screws	269028 20
Insert size	12 mm
suitable indexable insert	CC.. 1204..
Shank size	16 mm
ISO code toolholder	SCSCR/L 1616H12
Head length L ₁	22 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 20	269028 20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15