



## Short drill chuck Form A, SK 40, Clamping range: 2,5-16mm



### Order data

Order number	301565 2,5-16
GTIN	4045197931818
Item class	32K

### Description

#### Version:

For clockwise and anticlockwise rotation.  
Burnished. With Balluff/RFID chip bore.

#### Supplied with:

**Torx® chuck key** with T-handle **for high clamping force.**

#### Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

### Technical description

Clamping range	2.5 - 16 mm
Overhang dimension A	80 mm
Spare Torx® chuck key No. 625220	TX25
External Ø D	50 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 50 µm

maximum tightening torque $M_{d\max}$	$\leq 14$ Nm
Balluffchip bore	yes
Type of product	Short drill chuck