

Garant**Short drill chuck, VDI 30, Clamping range: 1-16mm****Order data**

Order number	319715 1-16
GTIN	4045197932037
Item class	31B

Description**Version:**

- Coolant supply via indexing bore.
- Maximum coolant pressure 50 bar.
- GARANT type with Torx® clamping wrench for high clamping force.

Application:

On NC turning machines and machining centres.

Standard:

DIN ISO 10889 / DIN 69880 / VDI 3425, Blatt 2.

Technical description

Clamping range	1 - 16 mm
Chuck key	TX25
Overhang l_1	90 mm
Chuck outside $\varnothing d_1$	50.5 mm
VDI size	VDI 30
Colour code for VDI shanks	VDI 30
Type of product	VDI keyless drill chucks

