

Garant**Clamping toolholder SSSCL 45°, for indexable inserts SC., left-hand, Shank / insert size: 10/09mm**

Order data

Order number	260707 10/09
GTIN	4045197937469
Item class	21T

Technical description

Pack of insert screws	269028 23
Insert size	9 mm
Shank size	10 mm
suitable indexable insert	SC.. 09T3..
Head length L ₁	21 mm
Overall length L	70 mm
Functional width L ₄	14.25 mm
ISO code toolholder	SSSCR/L 1010E09
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15