

**Short drill chuck Form A, BT 50, Clamping range: 2,5-16mm****Order data**

Order number	303166 2,5-16
GTIN	4045197937940
Item class	32K

Description**Version:**

For clockwise and anticlockwise rotation.

- **Slim design.**
- **Specific coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

Supplied with:

Clamping wrench.

Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping range	2.5 - 16 mm
External Ø D	50 mm
Overhang dimension A	106 mm
Spare Torx® chuck key No. 625220	TX25
Adapter	BT 50
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	A

Balance quality G at rotational speed	G 6.3 at 12,000 rpm
Concentricity	$\leq 50 \mu\text{m}$
maximum tightening torque $M_{d \max}$	$\leq 14 \text{ Nm}$
Type of product	Short drill chuck