

Garant

Steel boring bar A.. SVVCR 72,5°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 16/07mm

**Order data**

Order number	261352 16/07
GTIN	4045197941527
Item class	21T

Technical description

Centre offset L_3	11 mm
Overall length L	150 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
suitable indexable insert	VC.. 0702..
Insert size	7 mm
Clamping height L_2	15 mm
ISO code toolholder	A16M SVVCR/L07
Setting angle κ	72.5 degrees
Pack of insert screws	269028 27
Head length L_1	36 mm
Neck width L_4	12.9 mm
Usable depth T	6 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6