

**Garant**

**Steel boring bar A.. SVVCR 72,5°, for indexable inserts VC., right-hand, Shank Ø / insert size: 8/05mm**


**Order data**

Order number	261352 8/05
GTIN	4045197941558
Item class	21T

**Technical description**

ISO code toolholder	A08F SVVCR/L05
Insert size	5 mm
Overall length L	80 mm
Neck width L <sub>4</sub>	6 mm
Pack of insert screws	269028 26
Centre offset L <sub>3</sub>	5.5 mm
Setting angle κ	72.5 degrees
suitable indexable insert	VC.. 0501..
Minimum pre-drill Ø D <sub>min</sub>	10.2 mm
Head length L <sub>1</sub>	15 mm
Clamping height L <sub>2</sub>	7.5 mm
Usable depth T	3,5 mm
Shank Ø D <sub>s</sub>	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5	674248 TX5