

Garant

**Steel boring bar A.. SVLCR 95°, for indexable inserts VC.., right-hand, Shank
Ø / insert size: 12/07mm**

**Order data**

Order number	261346 12/07
GTIN	4045197941466
Item class	21T

Technical description

Centre offset L_3	9 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Neck width L_4	9 mm
Setting angle κ	95 degrees
Clamping height L_2	11 mm
Pack of insert screws	269028 27
suitable indexable insert	VC.. 0702..
Head length L_1	28 mm
Insert size	7 mm
Overall length L	125 mm

ISO code toolholder	A12K SVLCR/L07
Usable depth T	6 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659905 200
Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659956 200
Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX6	675155 TX6