

Garant
**Steel boring bar A.. SVLCR 95°, for indexable inserts VC., right-hand, Shank
 Ø / insert size: 16/07mm**

Order data

Order number	261346 16/07
GTIN	4045197941473
Item class	21T

Technical description

Setting angle κ	95 degrees
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
suitable indexable insert	VC.. 0702..
Head length L_1	36 mm
Clamping height L_2	15 mm
Insert size	7 mm
Overall length L	150 mm
ISO code toolholder	A16M SVLCR/L07
Neck width L_4	14.5 mm
Pack of insert screws	269028 27
Centre offset L_3	11 mm
Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659905 200
Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659956 200
Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX6	675155 TX6