

Garant

**Steel boring bar A.. SVVCL 72,5°, for indexable inserts VC., left-hand, Shank
Ø / insert size: 12/07mm**


Order data

Order number	261353 12/07
GTIN	4045197941572
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	15.5 mm
Overall length L	125 mm
Setting angle κ	72.5 degrees
Pack of insert screws	269028 27
suitable indexable insert	VC.. 0702..
Insert size	7 mm
Centre offset L_3	9 mm
Neck width L_4	9 mm
ISO code toolholder	A12K SVVCR/L07
Clamping height L_2	11 mm
Head length L_1	28 mm
Usable depth T	6 mm
Shank Ø D_s	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6