

**Garant**

**Steel boring bar A.. SVVCL 72,5°, for indexable inserts VC., left-hand, Shank Ø / insert size: 16/07mm**


**Order data**

Order number	261353 16/07
GTIN	4045197941565
Item class	21T

**Technical description**

Head length $L_1$	36 mm
ISO code toolholder	A16M SVVCR/L07
Setting angle $\kappa$	72.5 degrees
Clamping height $L_2$	15 mm
Pack of insert screws	269028 27
suitable indexable insert	VC.. 0702..
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Overall length $L$	150 mm
Centre offset $L_3$	11 mm
Insert size	7 mm
Neck width $L_4$	12.9 mm
Usable depth $T$	6 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6