

Garant

Steel boring bar A.. SVLCL 95°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 12/07mm

**Order data**

Order number	261347 12/07
GTIN	4045197941503
Item class	21T

Technical description

Pack of insert screws	269028 27
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Insert size	7 mm
Neck width L_4	9 mm
suitable indexable insert	VC.. 0702..
Centre offset L_3	9 mm
Head length L_1	28 mm
Overall length L	125 mm
Clamping height L_2	11 mm
ISO code toolholder	A12K SVLCLR/L07

Setting angle κ	95 degrees
Usable depth T	6 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659905 200
Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659956 200
Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX6	675155 TX6