

Garant

Steel boring bar A.. SVLCL 95°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 8/05mm


Order data

Order number	261347 8/05
GTIN	4045197941480
Item class	21T

Technical description

Head length L_1	15 mm
Overall length L	80 mm
Clamping height L_2	7.5 mm
ISO code toolholder	A08F SVLCR/L05
suitable indexable insert	VC.. 0501..
Insert size	5 mm
Neck width L_4	6 mm
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Pack of insert screws	269028 26
Setting angle κ	95 degrees
Centre offset L_3	5 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659905 200
Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659956 200
Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX5	675155 TX5