

Garant

Steel boring bar A.. SVVCR 72,5°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 10/07mm


Order data

Order number	261352 10/07
GTIN	4045197941541
Item class	21T

Technical description

suitable indexable insert	VC.. 0702..
Minimum pre-drill Ø D _{min}	13.5 mm
Insert size	7 mm
Neck width L ₄	6.8 mm
Setting angle κ	72.5 degrees
Head length L ₁	22 mm
Pack of insert screws	269028 27
Overall length L	100 mm
ISO code toolholder	A10H SVVCR/L07
Centre offset L ₃	8 mm
Clamping height L ₂	9 mm
Usable depth T	6 mm
Shank Ø D _s	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6