

**Garant**

**Steel boring bar A.. SVVCR 72,5°, for indexable inserts VC., right-hand, Shank Ø / insert size: 12/07mm**


**Order data**

Order number	261352 12/07
GTIN	4045197941534
Item class	21T

**Technical description**

Centre offset $L_3$	9 mm
Clamping height $L_2$	11 mm
Head length $L_1$	28 mm
Setting angle $\kappa$	72.5 degrees
ISO code toolholder	A12K SVVCR/L07
Minimum pre-drill $\varnothing D_{min}$	15.5 mm
Neck width $L_4$	9 mm
suitable indexable insert	VC.. 0702..
Overall length L	125 mm
Insert size	7 mm
Pack of insert screws	269028 27
Usable depth T	6 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6