



## Lever lock toolholder set, right-hand, Shank / insert size: 25mm



### Order data

Order number	255130 25
GTIN	4045197941732
Item class	29W

### Technical description

Shank size	25 mm
Overall length L	150 mm
Head length L <sub>1</sub>	25 mm
ISO code toolholder	PCLNR 2525M16; PDJNR 2525M15; PSSNR 2525M12
Functional width L <sub>4</sub>	32 mm
suitable indexable insert	CN.. 1606.; DN.. 1506.; SN.. 1204..
Spare part	259981 3
Standard	DIN ISO 5610
Application type	right-hand
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

**Accessories**

Lever lock toolholder Shank / insert size 25/16 mm	250018 25/16
Lever lock toolholder Shank / insert size 25/15 mm	250610 25/15
Lever lock toolholder Shank / insert size 25/12 mm	251112 25/12
Spare parts set for lever lock toolholder Type 3	259981 3