



Lever lock toolholder set, right-hand, Shank / insert size: 16mm



Order data

Order number	255130 16
GTIN	4045197941718
Item class	29W

Technical description

Head length L ₁	22 mm
Head length L ₁	25 mm
Head length L ₁	25 mm
ISO code toolholder	PCLNR 1616H09; PDJNR 1616H11; PSSNR 1616H12
suitable indexable insert	CN.. 09T3.; DN.. 1104.; SN.. 1204..
Shank size	16 mm
Functional width L ₄	20 mm
Overall length L	100 mm
Spare part	259981 1
Standard	DIN ISO 5610
Standard	Works standard

Application type	right-hand
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever lock toolholder Shank / insert size 16/09 mm	250018 16/09
Lever lock toolholder Shank / insert size 16/11 mm	250610 16/11
Lever lock toolholder Shank / insert size 16/12 mm	251112 16/12
Spare parts set for lever lock toolholder Type 1	259981 1