

Screw-on toolholder set, right-hand, Shank / insert size: 25mm



Order data

Order number	265130 25
GTIN	4045197941800
Item class	29W

Technical description

Head length L ₁	20 mm
Head length L ₁	21.5 mm
Head length L ₁	25 mm
Functional width L ₄	32 mm
Overall length L	150 mm
ISO code toolholder	SCLCR 2525M12; SDJCR 2525M11; SSSCR 2525M12
suitable indexable insert	CC.. 1204.; DC.. 11T3.; SC.. 1204
Shank size	25 mm
Spare part	269981 3
Standard	DIN ISO 5610
Application type	right-hand
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Spare parts set for screw-on toolholder Type 3	269981 3
Screw-on toolholder Shank / insert size 25/12 mm	260706 25/12
Screw-on toolholder Shank / insert size 25/12 mm	260006 25/12
Screw-on toolholder Shank / insert size 25/11 mm	260308 25/11