

**Screw-on toolholder set, right-hand, Shank / insert size: 12mm****Order data**

Order number	265130 12
GTIN	4045197941770
Item class	29W

**Technical description**

suitable indexable insert	CC.. 09T3.; DC.. 0702.; SC.. 09T3
ISO code toolholder	SCLCR 1212F09; SDJCR 1212F07; SSSCR 1212F09
Head length L <sub>1</sub>	13 mm
Head length L <sub>1</sub>	17 mm
Head length L <sub>1</sub>	20 mm
Overall length L	80 mm
Functional width L <sub>4</sub>	16 mm
Shank size	12 mm
Spare part	269981 1
Standard	DIN ISO 5610
Application type	right-hand

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Spare parts set for screw-on toolholder Type 1	269981 1
Screw-on toolholder Shank / insert size 12/09 mm	260706 12/09
Screw-on toolholder Shank / insert size 12/07 mm	260308 12/07
Screw-on toolholder Shank / insert size 12/09 mm	260006 12/09