



## Side lock arbor, HSK-A 63 short, Clamping range $\varnothing$ D1: 40mm



### Order data

Order number	304277 40
GTIN	4045197944252
Item class	32A

### Description

#### Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

#### Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

#### Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

#### Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

### Technical description

Clamping $\varnothing$ D <sub>1</sub>	40 mm
Overhang dimension A	125 mm
Adapter	HSK-A 63 short
Arbor standard	DIN 69893
Arbor standard	DIN 69882-4
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 20,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Side lock arbor