


Garant**ER collet chuck nickel-plated, HSK-A 100 long, for ER collet size: 40**

Order data

Order number	305486 40
GTIN	4045197945808
Item class	31A

Description

Version:

With Balluff/RFID chip bore.

- **All shanks hard turned (for smooth running!).**
- **Through bored (without adjustment screw).**
- **HSK mating faces machined.**

Nickel-plated to prevent corrosion.

Application:

For clamping tools with plain shanks in ER collets to DIN 6499 – Form A and B.

Supplied with:

Coated High-Speed clamping nut.

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, ER collets No. 308881 – 309434, ER chuck key No. 309680 or 613300.

Technical description

External Ø D	63 mm
Clamping range	3 - 26 mm
for ER collets	40
Overhang dimension A	120 mm

Adapter	HSK-A 100 long
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-6
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

Accessories

ER chuck key for ER collet chuck 40	309680 40
-------------------------------------	-----------