

Garant

Steel boring bar A.. SV95CR 95°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 10/07mm


Order data

Order number	261354 10/07
GTIN	4045197948045
Item class	21T

Technical description

Clamping height L_2	9 mm
ISO code toolholder	A10H SV95CR/L07
Head length L_1	22 mm
Overall length L	100 mm
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Pack of insert screws	269028 27
Setting angle κ	95 degrees
Insert size	7 mm
suitable indexable insert	VC.. 0702..
Centre offset L_3	7 mm
Neck width L_4	6.8 mm
Usable depth T	5 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD

Through-coolant	yes
Application	External longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6