

Garant

Steel boring bar A.. SV95CR 95°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 16/07mm


Order data

Order number	261354 16/07
GTIN	4045197948069
Item class	21T

Technical description

Head length L_1	36 mm
Neck width L_4	12.9 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Centre offset L_3	11 mm
Overall length L	150 mm
Clamping height L_2	15 mm
Insert size	7 mm
Setting angle κ	95 degrees
Pack of insert screws	269028 27
suitable indexable insert	VC.. 0702..
ISO code toolholder	A16M SV95CR/L07
Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD

Through-coolant	yes
Application	External longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6