

Garant

Steel boring bar A.. SV95CL 95°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 8/05mm


Order data

| | |
|--------------|---------------|
| Order number | 261355 8/05 |
| GTIN | 4045197948076 |
| Item class | 21T |

Technical description

| | |
|--|-----------------|
| Centre offset L_3 | 5 mm |
| Overall length L | 80 mm |
| Insert size | 5 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 9.2 mm |
| Pack of insert screws | 269028 26 |
| Neck width L_4 | 6 mm |
| suitable indexable insert | VC.. 0501.. |
| ISO code toolholder | A08F SV95CR/L05 |
| Clamping height L_2 | 7.5 mm |
| Setting angle κ | 95 degrees |
| Head length L_1 | 15 mm |
| Usable depth T | 3 mm |
| Shank $\varnothing D_s$ | 8 mm |
| Standard | Works standard |
| Application type | left-hand |
| Boring depth up to | 3×D |

| | |
|-----------------|-------------------------------|
| Through-coolant | yes |
| Application | External longitudinal turning |
| Type of product | Boring Bar |

Accessories

| | |
|--|------------|
| Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm | 659957 200 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5 | 674248 TX5 |